

Brinell Handness Testen

LCB-1000

QUALITY FUNCTIONALITY AND DESIGN FOR PERFECT HARDNESS TESTING





COMPLETE BRINELL HARDNESS TESTING

Highly accurate in determining Brinell Hardness values of materials which are used to evaluate its resistance to deformation, scratching, indentation, or penetration

APPLICATIONS

- Suitable for Brinell hardness in production, shop floor, and lab environments
- Ideal for low to medium testing volumes

FEATURES

Main Tester

- 1) Innovative closed-loop load cell technology
 - Eliminates the need for handling heavy weights or highmaintenance hydraulic load systems
 - Absence of mechanical weights eliminates friction and makes the tester less sensitive to misalignments caused by vibrations
 - Highly accurate measurements within 0.5% for all test loads
 - > Approximately 50% less weight than the traditional dead type tester.
- 2) Can be supplied with a built-in digital microscope, tablet PC with integrated automatic image analysis software, and/or automated test cycle.
- 3) The built-in Touch Screen will guide the operator through the selection process of proper Brinell scale for different materials and will inform the operator of what indenter needs to be utilised for the selected Brinell scale.
- 4) Selectable dwell time can be set via the Touch Screen Display.
- 5) Automatic test cycle
 - Load application, dwelling, and unloading is performed automatically.
 - Improves the accuracy and reproducibility of test results by reducing human operator interaction.
 - > The optional stepper motor can be supplied to automate the lifting and positioning of the test anvil prior to load application.
- 5) The fully automatic image analysis software can be installed on most modern desktop or laptop PCs and offers the following features:
 - > USB camera capture the indentation image, and powerful image analysis software measures the size of the indentation and automatically calculates the Brinell hardness value based on the applied load.



- USB connection to PC and supports Windows.
- A large number of results can be stored including the image from each test.
- Data can be exported to MS Excel or other software.
- Can perform measurements for all test loads between 62.5 kgf and 3000 kgf, for indenters 2.5 mm, 5mm, and 10mm, and for Brinell hardness values between 3.18 HBW and 658 HBW.

ADVANTAGES

- Greatly simplifies the indentation and measurement process, allowing for more accurate results more quickly than traditional testers.
- Can eliminate the need for separate microscope and PC.
- Market leading price-performance ratio.



THEORY AND METHOD

As explained in ASTM E10-18:

"The Brinell hardness test provides useful indentation information about metallic materials. This information may correlate to tensile strength, wear resistance, ductility, or other physical characteristics of metallic materials, and may be useful in quality control and selection of materials.

$$\mathrm{BHN} = \frac{2P}{\pi D \left(D - \sqrt{D^2 - d^2}\right)}$$

Brinell hardness tests are considered satisfactory for acceptance testing of commercial shipments.

An indenter of known diameter is pressed into a material with a known force load, typically measured in kilogram-force (kgf). The diameter of the indentation after the load is measured, and these values are input into the following formula:

Where

BHN = Brinell Hardness No.

P = Force load in kgf

D = Diameter of ball indenter (in mm)

d = Diameter of indentation (in mm)

TECHNICAL SPECIFICATIONS

Highly accurate in determining Brinell hardness values of materials which are used to evaluate its resistance to deformation, scratching, indentation, or penetration

Available Test Loads	kgf 62.5, 100, 125, 187.5, 250, 500, 750, 1000, 1500, 3000			
	N 612.9, 980, 1226, 1839, 2452, 4900, 7355, 9800, 14700, 29400			
Load Dwell Duration	2 s – 99 s, can be set by Touch screen and stored			
Tungsten Carbide Indenter	Ø10 mm included standard, Ø5 mm and Ø2.5 mm sizes ordered separately			
Standard Reference Blocks	125-350 HBW 10/3000, others available by request			
Measuring Range	3.18 HBW – 658 HBW			
Indentation Measurement Accuracy (QualiScope option)	± 0.5%			
Accuracy of Brinell Hardness Value	Hardness Range		Error (%)	Repeatability (%)
	HBW ≤ 125		± 2.5	≤ 3.0
	125 < HBW ≤ 225		± 2.0	≤ 2.5
	HBW > 225		± 1.5	≤ 2.0
Maximum Sample Height	220 mm			
Maximum Sample Depth	240 mm			
Power Supply	220 VAC, 50Hz, 4 A			

